



PL-T Triple 4-Pin Base Energy Advantage

PL-T 32W/830/XEW/A/4P/ALTO 27W

Philips Linear Compact Fluorescent Lamps offer designers, specifiers and end-users new levels of efficiencies and versatility in sizes, configurations and application possibilities. With so many elegant fixtures available to complement their small size, high light output and advanced technology, Philips Energy Advantage lamps are fast becoming the preferred choice when maximum efficiency and sleek design solutions are required.

Warnings and Safety

• Lamp contains mercury. Manage in Accord with Disposal Laws. See: www.lamprecycle.org or 1-800-555-0050

Product data

General Information		Color Rendering Index (Nom)	
Base	GX24Q-3 [GX24q-3]		>80
Life to 50% Failures Preheat (Nom)	16000 h	Operating and Electrical	
Features	ALTO® (ALTO)	Power (Rated) (Nom)	28 W
		Lamp Current (Nom)	0.320 A
Light Technical		Controls and Dimming	
Color Code	830 [CCT of 3000K]	Dimmable	Yes
Initial lumen (Nom)	1900 lm	Mechanical and Housing	
Color Designation	Warm White (WW)	Cap-Base Information	4P
Lumen Maintenance 2000 h (Nom)	92 %		
Lumen Maintenance 5000 h (Nom)	87 %		
Correlated Color Temperature (Nom)	3000 K		
Luminous Efficacy (rated) (Nom)	70 lm/W		

PL-T Triple 4-Pin Base Energy Advantage

Approval and Application

Mercury (Hg) Content (Nom) 1.4 mg

Product Data

Order product name PL-T 32W/830/XEW/A/4P/ALTO 27W

EAN/UPC - Product 046677220211

Order code 220210

Numerator - Quantity Per Pack 1

Numerator - Packs per outer box 10

Material Nr. (12NC) 927906983020


Net Weight (Piece) 70.000 g

Dimensional drawing

Product	D (max)	B (max)	C (max)
PL-T 32W/830/XEW/A/4P/ALTO 27W	41.0 mm	123.0 mm	138.7 mm

PL-T XEW 32W/830/4P ALTO 27W

Photometric data



LDPB_PLT4PXEW_830-Spectral power distribution B/W

LDPO_PLT4PXEW_830-Spectral power distribution Colour

