



# PL-T Triple 4-Pin Base

## PL-T 18W/841/A/4P/ALTO

Philips Linear Compact Fluorescent Lamps offer designers, specifiers and end-users new levels of efficiencies and versatility in sizes, configurations and application possibilities. With so many elegant fixtures available to complement their small size, high light output and advanced technology, Philips Energy Advantage lamps are fast becoming the preferred choice when maximum efficiency and sleek design solutions are required.

### Warnings and Safety

• Lamp contains mercury. Manage in Accord with Disposal Laws. See: [www.lamprecycle.org](http://www.lamprecycle.org) or 1-800-555-0050

### Product data

General Information		LLMF 4000 h Rated		88 %	
Base	GX24Q-2 [ GX24q-2]	LLMF 6000 h Rated		85 %	
LSF Preheat 2000 h Rated	99 %	LLMF 8000 h Rated		84 %	
LSF Preheat 4000 h Rated	98 %	LLMF 12000 h Rated		81 %	
LSF Preheat 6000 h Rated	97 %				
LSF Preheat 8000 h Rated	90 %				
Light Technical		Operating and Electrical			
Color Code	841 [ CCT of 4100K]	Power (Rated) (Nom)		18.0 W	
Initial lumen (Nom)	1175 lm	Lamp Current (Nom)		0.225 A	
Luminous Flux (Rated) (Nom)	1175 lm				
Color Designation	Cool White (CW)	Temperature			
Correlated Color Temperature (Nom)	4100 K	Design Temperature (Nom)		28 °C	
Luminous Efficacy (rated) (Nom)	65.3 lm/W				
Color Rendering Index (Nom)	80	Controls and Dimming			
LLMF 2000 h Rated	92 %	Dimmable		Yes	

# PL-T Triple 4-Pin Base

Mechanical and Housing	
Cap-Base Information	4P
Approval and Application	
Energy Efficiency Label (EEL)	B
Mercury (Hg) Content (Nom)	1.4 mg
Product Data	
Order product name	PL-T 18W/841/A/4P/ALTO

EAN/UPC - Product	046677268220
Order code	458232
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10
Material Nr. (12NC)	927910584150
Net Weight (Piece)	58.000 g
ILCOS Code	FSM-18/40/1B-E-GX24q=2


## Dimensional drawing

□


Product	D (max)	A (max)	B (max)	C (max)
PL-T 18W/841/A/4P/ALTO	41 mm	71.7 mm	96.0 mm	111.7 mm

PL-T ALTO 18W/841/4P A

## Lifetime




LDLM\_PLTTOP4P\_0001-Lumen maintenance diagram



LDLE\_PLTTOP4P\_0001-Life expectancy diagram

## PL-T Triple 4-Pin Base

### Lifetime



LDLE\_PLTTOP4P\_0002-Life expectancy diagram

