



# T5 High Output

## F39T5/841/HO/ALTO 40PK

Philips T5 HO lamps are environmentally-responsible, ultra-slim and have extraordinary light output and longer life.

### Warnings and Safety

· Lamp contains mercury. Manage in Accord with Disposal Laws. See: [www.lamprecycle.org](http://www.lamprecycle.org) or 1-800-555-0050

### Product data

General Information		Color Rendering Index (Nom)	
Base	G5 [ G5]		82
Life to 50% Failures Preheat (Nom)	30000 h	LLMF 2000 h Rated	96 %
Features	HO Alto® [ High Output Alto]	LLMF 4000 h Rated	95 %
System Description	High Output (HO)	LLMF 6000 h Rated	94 %
LSF Preheat 2000 h Rated	99 %	LLMF 8000 h Rated	93 %
LSF Preheat 4000 h Rated	99 %	LLMF 12000 h Rated	92 %
LSF Preheat 6000 h Rated	99 %	LLMF 16000 h Rated	91 %
LSF Preheat 8000 h Rated	99 %	LLMF 20000 h Rated	90 %
LSF Preheat 16000 h Rated	97 %		
LSF Preheat 20000 h Rated	84 %		
Light Technical		Operating and Electrical	
Color Code	841 [ CCT of 4100K]	Power (Rated) (Nom)	38.0 W
Initial lumen (Nom)	3500 lm	Lamp Current (Nom)	0.325 A
Luminous Flux (Rated) (Nom)	3100 lm		
Color Designation	Cool White (CW)	Temperature	
Luminous Efficacy (@ Max Lumen, Rated) (Nom)	92 lm/W	Design Temperature (Nom)	35 °C
Correlated Color Temperature (Nom)	4100 K		
Luminous Efficacy (rated) (Nom)	82 lm/W	Controls and Dimming	
Color Rendering Index (Max)	85	Dimmable	Yes
Color Rendering Index (Min)	80		
		Mechanical and Housing	
		Cap-Base Information	Green [ Green Cap]

# T5 High Output

## Approval and Application


Energy Efficiency Label (EEL)	A
Mercury (Hg) Content (Nom)	1.4 mg

## Product Data

Order product name	39W/841 Min Bipin T5 HO ALTO UNP
EAN/UPC - Product	046677290252
Order code	290254

Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	40
Material Nr. (12NC)	927992684022
Net Weight (Piece)	78.000 g
ILCOS Code	FDH-39/40/1B-L/P-G5-16/1150


## Dimensional drawing




Product	D (max)	A (max)	B (max)	B (min)	C (max)
39W/841 Min Bipin T5 HO	17 mm	849.0 mm	856.1 mm	853.7 mm	863.2 mm
ALTO UNP					

## TL5 HO F39T5/841 HO Alto

## Photometric data



LDPB\_TL5-HO8\_840-Spectral power distribution B/W



LDPO\_TL5-HO8\_840-Spectral power distribution Colour

# T5 High Output

## Lifetime



LDLE\_TL5-HO8\_0001-Life expectancy diagram

LDLE\_TL5-HO8\_0002-Life expectancy diagram



LDLM\_TL5-HO8\_0001-Lumen maintenance diagram

