



# MSR

## MSR 1200/2.1CT/3

The high color rendering index of the single ended MSR series ensures that everyone in the audience can enjoy the true colors of the scenery, the stage props, the players and their costumes – in fact everything that is on stage can be made bright and vivid in daylight quality light. Also, thanks to the single ended lamp concept, the luminaire has optimal light collection and direction possibilities to help ensure brightness on stage exactly where and when it is needed. In addition, the MSR can be used in any burning position for easy set-up and convenience.

### Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- Lamp contains mercury. Manage in Accord with Disposal Laws. See: [www.lamprecycle.org](http://www.lamprecycle.org) or 1-800-555-0050

### Product data

General Information	
Base	G22 [ G22]
Operating Position	Universal [ Universal]
Main Application	Studio/Disco
Life to 50% Failures (Nom)	800 h
System Description	Cold Strike

Light Technical	
Color Code	2
Initial lumen (Min)	93600 lm
Initial lumen (Nom)	104000 lm
Chromaticity Coordinate X (Nom)	302
Chromaticity Coordinate Y (Nom)	320
Correlated Color Temperature (Nom)	7200 K

Operating and Electrical	
Luminous Efficacy (rated) (Nom)	87 lm/W
Color Rendering Index (Nom)	85
Power (Rated) (Nom)	1200 W
Lamp Current (Nom)	13.8 A
Ignition Supply Voltage (Min)	207 V

Controls and Dimming	
Dimmable	No

Mechanical and Housing	
Cap-Base Information	30x53mm

# MSR

## Luminaire Design Requirements


Bulb Temperature (Max)	700 °C
Pinch Temperature (Max)	350 °C

## Product Data

Order product name	MSR 1200/2.1CT/3
EAN/UPC - Product	8727900911336

Order code	245563
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	3
Material Nr. (12NC)	928171805114
Net Weight (Piece)	0.150 kg

## Dimensional drawing



MSR 1200/2

Product	D (max)	O	L (min)	L (max)	L	C (max)	F
MSR 1200/2.1CT/3	40 mm	10.0 mm	84 mm	86 mm	85 mm	175 mm	53 mm

## Photometric data

