



MSR Gold™ MiniFastFit (DJ/Club)

MSR Gold™ 300/2 MiniFastFit 1CT/4

Thanks to the specially designed lamp base and lamp holder, the MSR Gold™ MiniFastFit takes just seconds to replace, to help ensure non-stop clubbing entertainment. In addition, the innovative gold plated pins ensure excellent current transfer to prolong lamp and lamp holder lifetimes and thereby reduce lamp replacement costs. Easy handling and small compact fixture designs are allowed by the lamps compact size, while the very short arc provides a high perceived brightness and high beam intensity.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- Lamp contains mercury. Manage in Accord with Disposal Laws. See: www.lamprecycle.org or 1-800-555-0050

Product data

General Information	
Base	PGJX28 [PGJX28]
Operating Position	Universal [Universal]
Main Application	Entertainment
Life to 50% Failures (Nom)	750 h
System Description	MiniFastFit
Light Technical	
Color Code	2
Initial lumen (Min)	19170 lm
Initial lumen (Nom)	21300 lm
Chromaticity Coordinate X (Nom)	288

Chromaticity Coordinate Y (Nom)	306
Correlated Color Temperature (Nom)	9300 K
Luminous Efficacy (Rated) (Min)	64 lm/W
Luminous Efficacy (rated) (Nom)	71 lm/W
Color Rendering Index (Nom)	80
Operating and Electrical	
Power (Rated) (Nom)	300 W
Lamp Current (Nom)	3.75 A
Ignition Supply Voltage (Min)	207 V

MSR Gold™ MiniFastFit (DJ/Club)

Controls and Dimming

Dimmable	Yes
----------	-----

Mechanical and Housing

Cap-Base Information	PGJX28
----------------------	--------

Luminaire Design Requirements

Bulb Temperature (Max)	950 °C
------------------------	--------

Pinch Temperature (Max)	500 °C
-------------------------	--------

Product Data

Order product name	MSR Gold™ 300/2 MiniFastFit 1CT/4
--------------------	-----------------------------------

EAN/UPC - Product	8718291221111
-------------------	---------------

Order code	287177
------------	--------

Numerator - Quantity Per Pack	1
-------------------------------	---

Numerator - Packs per outer box	4
---------------------------------	---

Material Nr. (12NC)	928177105115
---------------------	--------------

Net Weight (Piece)	0.062 kg
--------------------	----------

Dimensional drawing



Product	D (max)	O	L (min)	L (max)	L	C (max)
MSR Gold™ 300/2 MiniFastFit 1CT/4	23 mm	5.0 mm	65.8 mm	67.8 mm	66.8 mm	126 mm

MSR GOLD 300/2 MiniFastFit

