



MasterColor CDM-R111 Elite

MASTERColor CDM-R111 Elite 35W/930 GX8.5 10D

MasterColor CDM-R111 Elite combines the trendy look of 111 mm aluminum-reflector halogen lamps with the long life, high energy efficiency and crisp white light of MasterColor CDM.

Product data

General Information			
Base	GX8.5 [GX8.5]	Lumen Maintenance 2000 h (Nom)	90 %
Operating Position	Universal [Universal]	Lumen Maintenance 4000 h (Nom)	85 %
Life to 5% Failures (Nom)	8000 h	Design Mean Lumens	1200 lm
Life To 10% Failures (Nom)	5500 h	Chromaticity Coordinate X (Nom)	0.432
Life to 20% Failures (Nom)	10500 h	Chromaticity Coordinate Y (Nom)	0.392
Life to 50% Failures (Nom)	12000 h	Correlated Color Temperature (Nom)	3000 K
ANSI Code HID	C130/O	Luminous Efficacy (rated) (Nom)	37 lm/W
Switching Cycle	1050X	Color Rendering Index (Min)	87
		Color Rendering Index (Nom)	90
		LLMF At End Of Nominal Lifetime (Nom)	70 %
		Luminous Flux in 90° Cone (Rated)	1350 lm
Light Technical		Operating and Electrical	
Color Code	930 [CCT of 3000K]	Power (Rated) (Nom)	39.1 W
Beam Angle (Nom)	10 °	Lamp Current (EM) (Nom)	0.440 A
Beam Angle Technical (Nom)	9 °	Re-Ignition Time (Min) (Max)	15 min
Beam Angle Technical (Max)	11 °	Warm Up Time to 60% Light (Nom)	120 s
Beam Angle Technical (Min)	7 °	Ignition Time (Max)	30 s
Luminous Intensity (Min)	27000 cd	Voltage (Max)	97 V
Luminous Intensity (Nom)	36000 cd	Voltage (Min)	81 V
Beam Description	Spot		
Color Designation	Warm White (WW)		
Lumen Maintenance 12000 h (Nom)	70 %		


MasterColor CDM-R111 Elite

Voltage (Nom)	89 V
Controls and Dimming	
Dimmable	No
Run-Up Time 90% (Max)	3 min
Mechanical and Housing	
Bulb Finish	Reflector
Approval and Application	
Energy Efficiency Label (EEL)	B
Mercury (Hg) Content (Nom)	4.7 mg
Energy Consumption kWh/1000 h	43 kWh

Product Data

Order product name	MASTERColor CDM-R111 Elite 35W/930 GX8.5 10D
EAN/UPC - Product	046677430726
Order code	430728
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	6
Material Nr. (12NC)	928195305306
Net Weight (Piece)	0.096 kg
ILCOS Code	MRS/UB-35/930-H-GX8.5-111/88/10


Dimensional drawing




CDM-R111 Elite 35W/930 10D

Product	D (max)	C (max)
MASTERColor CDM-R111 Elite 35W/930 GX8.5 10D	111 mm	95 mm

Photometric data



LDPO_CDMR111E_0001-Spectral power distribution Colour



LDLD_CDMR111E_0001-Light distribution diagram

MasterColor CDM-R111 Elite

