



Switch Start Metal Halide Standard

MH400/U/ED28 3PK

High performance, Long life and Superior light quality A compact, energy efficient metal halide lamp that provides crisp, sparkling light with long life and high efficiency.

Warnings and Safety

- R "WARNING: These lamps can cause serious skin burn and eye inflammation from short wave ultraviolet radiation if outer envelope of the lamp is broken or punctured. Do not use where people will remain for more than a few minutes unless adequate shielding or other safety precautions are used. Certain lamps that will automatically extinguish when the outer envelope is broken or punctured are commercially available." This lamp complies with FDA radiation performance standard 21 CFR subchapter J. (USA: 21 CFR 1040.30 Canada: SOR/DORS/80-381)
- Lamp contains mercury. Manage in Accord with Disposal Laws. See: www.lamprecycle.org or 1-800-555-0050

Product data

General Information		Footnotes HID 2	
Base	E39 [Single Contact Mogul Screw]		Rated life: Vertical +/- 15 degrees. Other positions 75% of vertical life. (385)
Operating Position	Universal [Universal]		
Main Application	General Lighting (G)	Footnotes HID 3	Vertical lumens. Horizontal lumens 6%–10% lower. (393)
Life to 50% Failures (Nom)	20000 h		
ANSI Code HID	M59/E		
Footnotes HID 1	Requires a ballast specified or approved for Philips metal halide lamps, or one that is designed to operate all popular brands of metal halide lamps. 1000W types will operate from H36 conventional lag type ballast for Mercury Vapor lamps at ambient temperatures of 50 degrees F or higher. 1000W types must not be operated at 1500W. (377)		
		Light Technical	
		Color Code	640 [CCT of 4000K]
		Luminous Flux (Rated) (Min)	32000 lm
		Luminous Flux (Rated) (Nom)	36000 lm
		Color Designation	Cool White (CW)
		Design Mean Lumens	24000 lm
		Chromaticity Coordinate X (Nom)	0.390
		Chromaticity Coordinate Y (Nom)	0.400
		Correlated Color Temperature (Nom)	4000 K

Switch Start Metal Halide Standard

Luminous Efficacy (Rated) (Min)	80 lm/W
Luminous Efficacy (rated) (Nom)	90 lm/W
Color Rendering Index (Nom)	57

Operating and Electrical

Power (Rated) (Nom)	400 W
Lamp Current (Nom)	3.25 A
Ignition Supply Voltage (Min)	350 V
Re-Ignition Time (Min) (Max)	12 min
Ignition Time (Max)	120 s
Voltage (Max)	150 V
Voltage (Min)	120 V
Voltage (Nom)	135 V

Mechanical and Housing

Bulb Finish	Clear
Cap-Base Information	Brass [Brass Cap]
Bulb Material	Hard Glass

Approval and Application

Energy Saving Product	Not Applicable
Mercury (Hg) Content (Max)	52.0 mg


Luminaire Design Requirements

Bulb Temperature (Max)	400 °C
Cap-Base Temperature (Max)	250 °C

Product Data

Order product name	MH400/U/ED28 3PK
EAN/UPC - Product	046677253677
Order code	140848
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	3
Material Nr. (12NC)	928601151304
Net Weight (Piece)	0.001 kg

Dimensional drawing



MH R 400W/640 E39 ED28 U

Product	D	C (max)
MH400/U/ED28 3PK	3.5 in	8.313 in

