



LED Small Spots

5.5PAR16/AMB/F40/830/E26/DIM120V BC 1PK

Philips standard and Glass LED spots are a perfect fit for basic spot lighting and deliver warm halogen-like light. They are compatible with most existing fixtures with a GU10 socket and are designed as a retrofit replacement for halogen spots. They provide the beautiful light and performance you expect from the LED technology at an affordable price.

Product data


General Information		Lamp Current (Nom)	
Base	E26 [Single Contact Medium Screw]	Lamp Current (Nom)	55 mA
EU RoHS compliant	Yes	Wattage Equivalent	50 W
Nominal Lifetime (Nom)	25000 h	Starting Time (Nom)	0.5 s
Switching Cycle	25000X	Warm Up Time to 60% Light (Nom)	0.5 s
Technical Type	5.5-50W	Power Factor (Nom)	0.75
		Voltage (Nom)	120 V
Light Technical		Temperature	
Color Code	830 [CCT of 3000K]	T-Case Maximum (Nom)	80 °C
Beam Angle (Nom)	40 °		
Initial lumen (Nom)	400 lm	Controls and Dimming	
Luminous Intensity (Nom)	650 cd	Dimmable	Yes
Color Designation	White (WH)		
Correlated Color Temperature (Nom)	3000 K	Approval and Application	
Luminous Efficacy (rated) (Nom)	72.73 lm/W	Energy Efficiency Label (EEL)	Not applicable
Color Consistency	<6	Suitable For Accent Lighting	Yes
Color Rendering Index (Nom)	80	Energy Consumption kWh/1000 h	- kWh
LLMF At End Of Nominal Lifetime (Nom)	70 %		
Operating and Electrical		Product Data	
Input Frequency	60 Hz	Order product name	5.5PAR16/AMB/F40/830/E26/DIM120V BC 1PK
Power (Rated) (Nom)	5.5 W	EAN/UPC - Product	046677470043

LED Small Spots

Order code	470047
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	4
Material Nr. (12NC)	929001318103

Net Weight (Piece)	0.046 kg
--------------------	----------


Dimensional drawing




PAR16L 120V 7W-50W 400lm 40D 3000K E26 D

Product	5.5PAR16/AMB/F40/830/E26/DIM120V BC 1PK
---------	---


Photometric data



LEDspot E26 PAR16 3000K





LEDspot E26 PAR16 3000K



LEDspot E26 PAR16 3000K

LED Small Spots

Lifetime



LEDspot E26 PAR16 3000K

LEDspot E26 PAR16 3000K

