



# LED PAR30 S/L

## 10PAR30L/LED/840/F25/DIM/ULW/120V 6/1FB

Philips LED spots with a single optic beam, provide a clean beam that's free from shadows with beam angles from 15 and 40 degrees to suit every general lighting application.

### Product data


General Information	
Base	E26 [ Single Contact Medium Screw]
EU RoHS compliant	Yes
Nominal Lifetime (Nom)	25000 h
Switching Cycle	25000X
Technical Type	10-75W
Light Technical	
Color Code	841 [ CCT of 4100K (841)]
Beam Angle (Nom)	25 °
Initial lumen (Nom)	850 lm
Luminous Intensity (Nom)	3300 cd
Color Designation	Cool White (CW)
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	85.00 lm/W
Color Consistency	<6
Color Rendering Index (Nom)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	50 to 60 Hz
Power (Rated) (Nom)	10 W
Lamp Current (Nom)	86 mA
Wattage Equivalent	75 W

Starting Time (Nom)	0.5 s
Warm Up Time to 60% Light (Nom)	0.5 s
Power Factor (Nom)	0.9
Voltage (Nom)	120 V
Temperature	
T-Case Maximum (Nom)	67 °C
Controls and Dimming	
Dimmable	Yes
Approval and Application	
Energy Efficiency Label (EEL)	Not applicable
Suitable For Accent Lighting	Yes
Energy Consumption kWh/1000 h	- kWh
Product Data	
Order product name	10PAR30L/LED/840/F25/DIM/ULW/120V 6/1FB
EAN/UPC - Product	046677529727
Order code	529727
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	6
Material Nr. (12NC)	929001321804

# LED PAR30 S/L

Net Weight (Piece)	0.285 kg
--------------------	----------



## Dimensional drawing



Glass UL wet PAR30L 120V 9-75W 850lm 25D


Product	D	C
10PAR30L/LED/840/F25/DIM/ULW/120V 6/1FB	94 mm	118 mm

## Photometric data



10-75W E26 PAR30L 25D 840 4000K



10-75W E26 PAR30L 25D 840 4000K



10-75W E26 PAR30L

# LED PAR30 S/L

## Lifetime



14-120W E26 PAR38

14-120W E26 PAR38

