



LED MR16

6.5MR16/LED/F35/930/D/EC/12V T20 10/1FB

Philips LED MR-16 lamps with single optic technology provide the look and color quality of traditional halogens while using a fraction of the energy. A perfect fit for spot lighting, they are compatible with most existing fixtures with MR16 GU5.3 holders and are designed as a retrofit replacement for halogen or incandescent spots.

Product data

General Information	
Base	GU5.3 [GU5.3]
EU RoHS compliant	Yes
Nominal Lifetime (Nom)	25000 h
Switching Cycle	50000X
Technical Type	6.5-42W

Light Technical	
Color Code	930 [CCT of 3000K]
Beam Angle (Nom)	35 °
Initial lumen (Nom)	485 lm
Luminous Intensity (Nom)	1110 cd
Color Designation	White (WH)
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	74.00 lm/W
Color Consistency	<3
Color Rendering Index (Nom)	91
LLMF At End Of Nominal Lifetime (Nom)	70 %

Operating and Electrical	
Input Frequency	- Hz
Power (Rated) (Nom)	6.5 W

Temperature	
T-Case Maximum (Nom)	92 °C



Controls and Dimming	
Dimmable	Yes

Approval and Application	
Energy Efficiency Label (EEL)	Not applicable
Suitable For Accent Lighting	Yes
Energy Consumption kWh/1000 h	- kWh

Product Data	
Order product name	6.5MR16/LED/F35/930/D/EC/12V T20 10/1FB
EAN/UPC - Product	046677479176
Order code	479170

LED MR16

Lifetime



LEDspot 6.5W GU5.3 MR16 927 25D DIM

LEDspot 6.5W GU5.3 MR16 927 25D DIM

