



TrueForce High Lumen PAR

23PAR30s/PER/930/S15/ND/120V 6/1FB

Philips LED TrueForce PAR high lumen lamps are the perfect transition from CDM lamps to LED.

Product data

General Information	
Base	E26 [Single Contact Medium Screw]
EU RoHS compliant	Yes
Nominal Lifetime (Nom)	25000 h
Switching Cycle	50000X
Technical Type	23-75W

Light Technical	
Color Code	930 [CCT of 3000K]
Beam Angle (Nom)	15°
Initial lumen (Nom)	1900 lm
Luminous Intensity (Nom)	12000 cd
Color Designation	White (WH)
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	82.00 lm/W
Color Consistency	<4
Color Rendering Index (Nom)	90
LLMF At End Of Nominal Lifetime (Nom)	70 %

Operating and Electrical	
Input Frequency	50 to 60 Hz
Power (Rated) (Nom)	23 W

Lamp Current (Nom)	206 mA
Wattage Equivalent	75 W
Starting Time (Nom)	0.5 s
Warm Up Time to 60% Light (Nom)	0.5 s
Power Factor (Nom)	0.9
Voltage (Nom)	120 V

Temperature	
T-Case Maximum (Nom)	94 °C

Controls and Dimming	
Dimmable	No

Approval and Application	
Energy Efficiency Label (EEL)	Not applicable
Suitable For Accent Lighting	Yes
Energy Consumption kWh/1000 h	- kWh


Product Data	
Order product name	23PAR30s/PER/930/S15/ND/120V 6/1FB
EAN/UPC - Product	046677534684
Order code	534685

TrueForce High Lumen PAR

Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	6
Material Nr. (12NC)	929001917404

Net Weight (Piece)	0.220 kg
--------------------	----------



Dimensional drawing



PAR30s 24.5-W 2000lm 15D 3000K E26 ND

Product	D	C
23PAR30s/PER/930/S15/ND/120V 6/1FB	96 mm	94 mm


Photometric data



LEDspot PAR30 1FB

LEDspot PAR30 1FB



LEDspot 23 PAR30L 930 S15



LEDspot 23 PAR30L 930 S15

TrueForce High Lumen PAR

Lifetime



LEDspot PAR30 1FB

LEDspot PAR30 1FB

