



# TrueForce High Lumen PAR

## 33PAR38/PER/830/S15/DIM/120V B 6/1FB

Philips LED TrueForce PAR high lumen lamps are the perfect transition from CDM lamps to LED.

### Product data


General Information		Lamp Current (Nom)	
Base	E26 [ Single Contact Medium Screw]		300 mA
EU RoHS compliant	Yes	Wattage Equivalent	250 W
Nominal Lifetime (Nom)	25000 h	Starting Time (Nom)	0.5 s
Switching Cycle	50000X	Warm Up Time to 60% Light (Nom)	0.5 s
Technical Type	33-250W	Power Factor (Nom)	0.95
		Voltage (Nom)	120 V
Light Technical		Temperature	
Color Code	830 [ CCT of 3000K]	T-Case Maximum (Nom)	90 °C
Beam Angle (Nom)	15 °		
Initial lumen (Nom)	3000 lm	Controls and Dimming	
Luminous Intensity (Nom)	35000 cd	Dimmable	Yes
Color Designation	White (WH)		
Correlated Color Temperature (Nom)	3000 K	Approval and Application	
Luminous Efficacy (rated) (Nom)	90.00 lm/W	Energy Efficiency Label (EEL)	Not applicable
Color Consistency	<4	Suitable For Accent Lighting	Yes
Color Rendering Index (Nom)	80	Energy Consumption kWh/1000 h	- kWh
LLMF At End Of Nominal Lifetime (Nom)	70 %		
Operating and Electrical		Product Data	
Input Frequency	50 to 60 Hz	Order product name	33PAR38/PER/830/S15/DIM/120V B 6/1FB
Power (Rated) (Nom)	33 W	EAN/UPC - Product	046677534622
		Order code	534628

# TrueForce High Lumen PAR

Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	6
Material Nr. (12NC)	929001919604

Net Weight (Piece)	0.425 kg
--------------------	----------


## Dimensional drawing




PAR38 120V 32-W 2800lm 15D 3000K E26 D

Product	D	C
33PAR38/PER/830/S15/DIM/120V B 6/1FB	123 mm	133 mm


## Photometric data



LEDSpot 33W E26 PAR38 S15 B





LEDSpot 33W E26 PAR38



LEDSpot 33W E26 PAR38 S15

# TrueForce High Lumen PAR

## Lifetime



LEDSpot 33W E26 PAR38

LEDSpot 33W E26 PAR38

