



# TrueForce High Lumen PAR

## 33PAR38/PER/830/F25/DIM/120V B 6/1FB

Philips LED TrueForce PAR high lumen lamps are the perfect transition from CDM lamps to LED.

### Product data

General Information	
Base	E26 [ Single Contact Medium Screw]
EU RoHS compliant	Yes
Nominal Lifetime (Nom)	25000 h
Switching Cycle	50000X
Technical Type	33-250W

Light Technical	
Color Code	830 [ CCT of 3000K]
Beam Angle (Nom)	25 °
Initial lumen (Nom)	3000 lm
Luminous Intensity (Nom)	10000 cd
Color Designation	White (WH)
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	90.00 lm/W
Color Consistency	<4
Color Rendering Index (Nom)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %

Operating and Electrical	
Input Frequency	50 to 60 Hz
Power (Rated) (Nom)	33 W

Lamp Current (Nom)	300 mA
Wattage Equivalent	250 W
Starting Time (Nom)	0.5 s
Warm Up Time to 60% Light (Nom)	0.5 s
Power Factor (Nom)	0.95
Voltage (Nom)	120 V

Temperature	
T-Case Maximum (Nom)	90 °C

Controls and Dimming	
Dimmable	Yes

Approval and Application	
Energy Efficiency Label (EEL)	Not applicable
Suitable For Accent Lighting	Yes
Energy Consumption kWh/1000 h	- kWh


Product Data	
Order product name	33PAR38/PER/830/F25/DIM/120V B 6/1FB
EAN/UPC - Product	046677534639
Order code	534636

# TrueForce High Lumen PAR

Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	6
Material Nr. (12NC)	929001919704

Net Weight (Piece)	0.430 kg
--------------------	----------


## Dimensional drawing




PAR38 120V 32-W 2800lm 25D 3000K E26 D

Product	D	C
33PAR38/PER/830/F25/DIM/120V B 6/1FB	123 mm	133 mm

## Photometric data




Standard Photometric Data Page Lighting 1/11 Page 1/11



LEDspot 33W E26 PAR38 F25 B



LEDspot 33W E26 PAR38 F25



LEDspot 33W E26 PAR38

# TrueForce High Lumen PAR

## Lifetime



LEDSpot 33W E26 PAR38

LEDSpot 33W E26 PAR38

