

LED Designer Deco

7.5G63/VIN/820/CL/G/DIM 2/1CT

Philips LED Designer Deco lamps allow you to maintain a warm, classic light or a modern, chic effect while providing longer life and energy savings


Product data

General Information	
Base	E26 [Single Contact Medium Screw]
EU RoHS compliant	Yes
Nominal Lifetime (Nom)	15000 h
Switching Cycle	20000X
Technical Type	7.5-40W
Light Technical	
Color Code	820 [CCT of 2000K]
Initial lumen (Nom)	400 lm
Color Designation	Flame
Correlated Color Temperature (Nom)	2000 K
Luminous Efficacy (rated) (Nom)	53.00 lm/W
Color Consistency	<6
Color Rendering Index (Nom)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	50 to 60 Hz
Power (Rated) (Nom)	7.5 W
Lamp Current (Nom)	70 mA
Wattage Equivalent	40 W
Starting Time (Nom)	0.5 s
Warm Up Time to 60% Light (Nom)	0.5 s

Power Factor (Nom)	0.7
Voltage (Nom)	120 V
Temperature	
T-Case Maximum (Nom)	45 °C
Controls and Dimming	
Dimmable	Yes
Approval and Application	
Energy Efficiency Label (EEL)	Not applicable
Energy Consumption kWh/1000 h	- kWh
Product Data	
Order product name	7.5G63/VIN/820/CL/G/DIM 2/1CT
EAN/UPC - Product	046677536268
Order code	536268
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	2
Material Nr. (12NC)	929001936303
Net Weight (Piece)	0.360 kg

LED Designer Deco


Dimensional drawing




Bulb G200 120V 8-40W 450lm 2000K E26 D

Product	D	C
7.5G63/VIN/820/CL/G/DIM 2/1CT	200 mm	285 mm


Photometric data



LEDbulb E26 40W





LEDbulb E26 G63 40W



LEDbulb E26 G63 40W

Lifetime



LEDbulb E26 D

LEDbulb E26 D

