



LED Designer Deco

7.5T20/modern/840/CL/G/DIM 2/1CT

Philips LED Designer Deco lamps allow you to maintain a warm, classic light or a modern, chic effect while providing longer life and energy savings


Product data

| General Information | |
|---------------------------------------|------------------------------------|
| Base | E26 [Single Contact Medium Screw] |
| EU RoHS compliant | Yes |
| Nominal Lifetime (Nom) | 15000 h |
| Switching Cycle | 20000X |
| Technical Type | 7.5-25W |
| Light Technical | |
| Color Code | 841 [CCT of 4100K (841)] |
| Initial lumen (Nom) | 250 lm |
| Color Designation | Cool White (CW) |
| Correlated Color Temperature (Nom) | 4000 K |
| Luminous Efficacy (rated) (Nom) | 33.00 lm/W |
| Color Consistency | <6 |
| Color Rendering Index (Nom) | 80 |
| LLMF At End Of Nominal Lifetime (Nom) | 70 % |
| Operating and Electrical | |
| Input Frequency | 50 to 60 Hz |
| Power (Rated) (Nom) | 7.5 W |
| Lamp Current (Nom) | 70 mA |
| Wattage Equivalent | 25 W |
| Starting Time (Nom) | 0.5 s |
| Warm Up Time to 60% Light (Nom) | 0.5 s |

| Power Factor (Nom) | 0.7 |
|---------------------------------|----------------------------------|
| Voltage (Nom) | 120 V |
| Temperature | |
| T-Case Maximum (Nom) | 45 °C |
| Controls and Dimming | |
| Dimmable | Yes |
| Approval and Application | |
| Energy Efficiency Label (EEL) | Not applicable |
| Energy Consumption kWh/1000 h | - kWh |
| Product Data | |
| Order product name | 7.5T20/modern/840/CL/G/DIM 2/1CT |
| EAN/UPC - Product | 046677536312 |
| Order code | 536318 |
| Numerator - Quantity Per Pack | 1 |
| Numerator - Packs per outer box | 2 |
| Material Nr. (12NC) | 929001936803 |
| Net Weight (Piece) | 0.196 kg |

LED Designer Deco



Dimensional drawing



Bulb T65 120V 7-40W 450lm 3500K E26 D


| Product | D | C |
|----------------------------------|-------|--------|
| 7.5T20/modern/840/CL/G/DIM 2/1CT | 65 mm | 272 mm |

Photometric data





LEDbulb E26 T20 25W

LEDbulb E26 G63 25W



LEDbulb E26 40W

Lifetime



LEDbulb E26 D

LEDbulb E26 D

