



LED A15

8A15/PER/950/CL/G/E26/DIM 1FB T20

Philips A15 LED Lamps offer energy saving ambience with an elegant effect. Their unique design provides light in all directions, giving lighting designers a long life alternative to standard incandescent sources.


Product data

General Information	
Base	E26 [Single Contact Medium Screw]
EU RoHS compliant	Yes
Nominal Lifetime (Nom)	15000 h
Switching Cycle	20000X
Technical Type	8-60W
Light Technical	
Color Code	950 [CCT of 5000K]
Initial lumen (Nom)	800 lm
Color Designation	Daylight
Correlated Color Temperature (Nom)	5000 K
Luminous Efficacy (rated) (Nom)	100.00 lm/W
Color Consistency	<4
Color Rendering Index (Nom)	90
LLMF At End Of Nominal Lifetime (Nom)	0.7 %
Operating and Electrical	
Input Frequency	60 Hz
Power (Rated) (Nom)	8 W
Lamp Current (Nom)	90 mA
Wattage Equivalent	60 W
Starting Time (Nom)	0.5 s
Warm Up Time to 60% Light (Nom)	0.5 s

Power Factor (Nom)	0.7
Voltage (Nom)	120 V
Temperature	
T-Case Maximum (Nom)	60 °C
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Clear
Approval and Application	
Energy Efficiency Label (EEL)	Not applicable
Energy Consumption kWh/1000 h	- kWh
Product Data	
Order product name	8A15/PER/950/CL/G/E26/DIM 1FB T20
EAN/UPC - Product	046677548315
Order code	548313
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10
Material Nr. (12NC)	929002209304
Net Weight (Piece)	0.020 kg

LED A15



Dimensional drawing



A15 120V 60W 800lm 5000K E26 D CL

Product	D	C
8A15/PER/950/CL/G/E26/DIM 1FB T20	47 mm	86 mm


Photometric data



OSRAM Research Ltd. All rights reserved. Page 1/1

LEDbulb 40,60W E26 950 CL,FR



LEDbulb 60W E26 A15 950 CL



LEDbulb 40,60W E26 950

LED A15

Lifetime



15K LED

15K LMP

