



LED Specialty Lamps

2T5/LED/830/ND/12V/BC/2PK 6/2

Philips speciality LED lamps are the smart alternative to standard incandescent. Their unique lamp design provides form factors to fit in standard applications with incredible energy savings.


Product data

General Information	
Base	Wedgebase
EU RoHS compliant	Yes
Nominal Lifetime (Nom)	15000 h
Switching Cycle	50000X
Technical Type	2-18W
Light Technical	
Color Code	830 [CCT of 3000K]
Initial lumen (Nom)	200 lm
Color Designation	White (WH)
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	100.00 lm/W
Color Consistency	<6
Color Rendering Index (Nom)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	- Hz
Power (Rated) (Nom)	2 W
Lamp Current (Nom)	260 mA
Wattage Equivalent	18 W
Starting Time (Nom)	0.5 s
Warm Up Time to 60% Light (Nom)	0.5 s

Power Factor (Nom)	0.6
Voltage (Nom)	ac electronic 12 V
Temperature	
T-Case Maximum (Nom)	80 °C
Controls and Dimming	
Dimmable	No
Approval and Application	
Energy Efficiency Label (EEL)	A++
Suitable For Accent Lighting	No
Energy Consumption kWh/1000 h	3 kWh
Product Data	
Order product name	2T5/LED/830/ND/12V/BC/2PK 6/2
EAN/UPC - Product	50046677475418
Order code	475418
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	6
Material Nr. (12NC)	929002389636
Net Weight (Piece)	0.008 kg

LED Specialty Lamps


Dimensional drawing




Wedge 2W-18W 200lm 3000K Non-Dim

Product	D	C
2T5/LED/830/ND/12V/BC/2PK 6/2	13 mm	34 mm

Photometric data




© 2020 Philips Lighting B.V. Page 1/1



LEDcapsule 2W Wedgebase 830



LEDcapsule 2W Wedgebase



LEDcapsule 2W Wedgebase 830

LED Specialty Lamps

Lifetime



15K LED

15K LMP

