



LED Wallpack Retrofits

20WP/LED/850/ND E26 G2 BB 6/1

Philips LED HID replacement lamps are perfect LED replacement for a variety of outdoor applications. High intensity illumination, which means you get added visibility for applications like streets, public areas, and much more for a fraction of the energy used by conventional HID.

Product data

General Information		Lamp Current (Nom)	
Base	E26 [Single Contact Medium Screw]		222 mA
EU RoHS compliant	Yes	Starting Time (Nom)	1 s
Nominal Lifetime (Nom)	50000 h	Warm Up Time to 60% Light (Nom)	1 s
Switching Cycle	50000X	Power Factor (Nom)	0.9
Technical Type	20-70-100W	Voltage (Nom)	100-277 V
Light Technical		Temperature	
Color Code	850 [CCT of 5000K]	T-Case Maximum (Nom)	60 °C
Initial lumen (Nom)	3000 lm	Controls and Dimming	
Color Designation	Daylight	Dimmable	No
Correlated Color Temperature (Nom)	5000 K	Mechanical and Housing	
Luminous Efficacy (rated) (Nom)	150.00 lm/W	Bulb Finish	Clear
Color Consistency	ANSI 5000K quadrangle	Approval and Application	
Color Rendering Index (Nom)	80	Energy Efficiency Label (EEL)	A++
LLMF At End Of Nominal Lifetime (Nom)	70 %	Energy Consumption kWh/1000 h	20 kWh
Operating and Electrical			
Input Frequency	50 to 60 Hz		
Power (Rated) (Nom)	20 W		


LED Wallpack Retrofits

Product Data

Order product name	20WP/LED/850/ND E26 G2 BB 6/1
EAN/UPC - Product	046677559922
Order code	559922
Numerator - Quantity Per Pack	1

Numerator - Packs per outer box	6
Material Nr. (12NC)	929002398104
Net Weight (Piece)	0.486 kg


Dimensional drawing




Wallpack LED 20W E26 850 CL

Product	D	C
20WP/LED/850/ND E26 G2 BB 6/1	92 mm	135 mm


Photometric data



LEDTForce 20W WallPack E26 850





LEDTForce 20W WallPack E26 850



LEDTForce WallPack

LED Wallpack Retrofits

Lifetime



50K

50K

