



# LED Wallpack Retrofits

## 60WP/LED/840/ND EX39 G2 BB 6/1

Philips LED HID replacement lamps are perfect LED replacement for a variety of outdoor applications. High intensity illumination, which means you get added visibility for applications like streets, public areas, and much more for a fraction of the energy used by conventional HID.

### Product data

General Information		Lamp Current (Nom)	
Base	EX39 [ Exclusionary Mogul Screw]	Lamp Current (Nom)	666 mA
EU RoHS compliant	Yes	Starting Time (Nom)	1 s
Nominal Lifetime (Nom)	50000 h	Warm Up Time to 60% Light (Nom)	1 s
Switching Cycle	50000X	Power Factor (Nom)	0.9
Technical Type	60-175-250W	Voltage (Nom)	100-277 V
Light Technical		Temperature	
Color Code	841 [ CCT of 4100K (841)]	T-Case Maximum (Nom)	65 °C
Initial lumen (Nom)	8700 lm	Controls and Dimming	
Color Designation	Cool White (CW)	Dimmable	No
Correlated Color Temperature (Nom)	4000 K	Mechanical and Housing	
Luminous Efficacy (rated) (Nom)	145.00 lm/W	Bulb Finish	Clear
Color Consistency	ANSI 4000K quadrangle	Approval and Application	
Color Rendering Index (Nom)	80	Energy Efficiency Label (EEL)	A++
LLMF At End Of Nominal Lifetime (Nom)	70 %	Energy Consumption kWh/1000 h	60 kWh
Operating and Electrical			
Input Frequency	50 to 60 Hz		
Power (Rated) (Nom)	60 W		


# LED Wallpack Retrofits

## Product Data

Order product name	60WP/LED/840/ND EX39 G2 BB 6/1
EAN/UPC - Product	046677559960
Order code	559962
Numerator - Quantity Per Pack	1

Numerator - Packs per outer box	6
Material Nr. (12NC)	929002398404
Net Weight (Piece)	0.950 kg


## Dimensional drawing




Wallpack LED 60W EX39 840 CL

Product	D	C
60WP/LED/840/ND EX39 G2 BB 6/1	92 mm	270 mm


## Photometric data



LEDTForce 60W WallPack EX39 840





LEDTForce WallPack



LEDTForce 60W WallPack EX39 840

# LED Wallpack Retrofits

## Lifetime



50K

50K

