



LED Wallpack Retrofits

60WP/LED/850/ND EX39 G2 BB 6/1

Philips LED HID replacement lamps are perfect LED replacement for a variety of outdoor applications. High intensity illumination, which means you get added visibility for applications like streets, public areas, and much more for a fraction of the energy used by conventional HID.

Product data

General Information	
Base	EX39 [Exclusionary Mogul Screw]
EU RoHS compliant	Yes
Nominal Lifetime (Nom)	50000 h
Switching Cycle	50000X
Technical Type	60-175-250W
Light Technical	
Color Code	850 [CCT of 5000K]
Initial lumen (Nom)	9000 lm
Color Designation	Daylight
Correlated Color Temperature (Nom)	5000 K
Luminous Efficacy (rated) (Nom)	150.00 lm/W
Color Consistency	ANSI 5000K quadrangle
Color Rendering Index (Nom)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	50 to 60 Hz
Power (Rated) (Nom)	60 W

Lamp Current (Nom)	666 mA
Starting Time (Nom)	1 s
Warm Up Time to 60% Light (Nom)	1 s
Power Factor (Nom)	0.9
Voltage (Nom)	100-277 V
Temperature	
T-Case Maximum (Nom)	65 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Clear
Approval and Application	
Energy Efficiency Label (EEL)	A++
Energy Consumption kWh/1000 h	60 kWh


LED Wallpack Retrofits

Product Data

Order product name	60WP/LED/850/ND EX39 G2 BB 6/1
EAN/UPC - Product	046677559953
Order code	559954
Numerator - Quantity Per Pack	1

Numerator - Packs per outer box	6
Material Nr. (12NC)	929002398504
Net Weight (Piece)	0.950 kg


Dimensional drawing




Wallpack LED 60W EX39 850 CL

Product	D	C
60WP/LED/850/ND EX39 G2 BB 6/1	92 mm	270 mm


Photometric data



LEDForce 60W WallPack EX39 850





LEDForce 60W WallPack EX39 850



LEDForce WallPack

LED Wallpack Retrofits

Lifetime



50K

50K

