



# OccuSwitch Classic Wallbox

Wall switch sensor, multi-tech dual switch, 120/277VAC

Wall switch sensor, multi-tech dual switch, 120/277VAC

OccuSwitch wall switch and low voltage occupancy sensors automatically turn lights off when a work space is unoccupied, saving energy and creating a more sustainable work environment. The ceiling mounted sensor communicates with a network of wall switches and dimmers. Using a combination of ultrasonic and passive infrared (PIR) technology, the sensor recognizes room occupancy or vacancy for maximum performance and energy savings.

## Product data

General Information	
Downlight Type	Controls
Mounting	Wall Surface
Operating and Electrical	
Voltages	120/277 V
Mechanical and Housing	
Shape	Rectangular

Product Data	
Order product name	Wall switch sensor, multi-tech dual switch, 120/277VAC
Order code	LRS2225
Material Nr. (12NC)	PLC00000059
Commercial Code	LRS2225
Catalog Number Description	Wall switch sensor, multi-tech dual switch, 120/277VAC